M18 BLHIWF12-OX

M18™ BRUSHLESS ½″ HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

- Delivers 1085 Nm of fastening torque and 1627 Nm of nut-busting torque to easily work with most occasional applications
- 222 mm body allows for more access in tight spaces
- Integrated LED light to illuminate the working area
- A speed of 1750 RPM to do your task quickly and efficiently
- Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	0 - 1750
Impact rate (ipm)	0 - 2000
Max. torque (Nm)	
Nut-busting torque (Nm)	1627
Weight with battery pack (EPTA) (kg)	3.4 (M18 B5)
Kit included	No batteries supplied, No charger supplied, HD Box
Article Number	4933492787