



CRZ 1362

ROHS COMPLIANT



Part-No. / 产品号码	Length / 长度
33 15 243 050 0015 .00	500±5
33 15 243 020 0014 .00	200±3
33 15 243 010 0013 .00	100±3

- NOTES/要求:
- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.
  - 2.) CABLE OPERATION TEMPERATURE= -30° C TO +105° C.
  - 3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION  
HARTING P/N & REVISION

Rev.	Description	Appr.	Date
01	Add side view.	LUCY/Z	15/04/13
00	Prototype	Andr-ew/H	15/1/13

All Dimensions in mm Original Size DIN A4		Ref. MB
Free size tol.	cm <sup>3</sup> A =	SEE BILL OF MATERIAL
V =	cm <sup>2</sup>	
Detail	Name	Title
Insp.	Date	Har-Flex female 50pole, double ended
Approved	Scale	Flat cable assembly, L=xMM
	Sheet	
	1 of 1	

HARTING (Zhuhai) Manufacturing Co., Ltd.			DWG. No.
			TB_33 15 0005 .01

4

3

2

1

A

B

C

D