



Datasheet

Stock No: 466-255

ENGLISH

RS Pro 8 Pole DIN Rail, Panel Mount Non-Fused Switch Disconnecter, 25 A, 11 kW, IP65



Product Details

Boxed Isolators

RS Pro high quality range of boxed isolator switch disconnectors for use with low voltage switchgear such as power distribution, load isolation and motor start/stop. The RS Pro range comes in 3 and 4 pole versions and has a power output available up to 90 kW.

Interlocking lid ensures removal in the OFF position only

Easy access and switch removal

Padlockable handles

Flame retardant material

Maximum voltage 750V

ABS, metal clad and diecast versions available

Standards

EN60947



ENGLISH

Specifications:

Number of Poles	8
Maximum Current	25 A
Mounting Type	DIN Rail, Panel
Power Rating	11 kW
IP Rating	IP65
Accepts Padlocks	Yes
Voltage Rating	690 V ac
Switch Rating	5 kA
Length	280mm
Width	190mm
Depth	130mm
Terminal Type	Wire Lead
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-25°C
Handle Colour	Red