

Datasheet

RS PRO PC-INSULATED PIGGY BACK DISCONNECTORS

Stock number: 613-9918

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	3	4	7	10


MAXIMUM ELECTRICAL RATING: 125° C 300 VOLTS MAX.

INSULATION MATERIAL: PC

TERMINAL MATERIAL: BRASS

INSULATION COLOR: RED

TERMINAL BARREL I.D.: C=1.7MM



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION inch(mm)							
			W	W1	F	F1	L	B	D	T
22-16 A.W.G. 0.5-1.5 mm ²	<input type="checkbox"/> 613-9918	.032X.250 (0.8X6.35)	0.26 6.6	0.25 6.35	0.315 8	0.323 8.2	0.906 23	0.433 11	0.157 4.000	0.016 0.04