

Features

- Under Bench Earth Bonding Bracket
- Designed to be fixed to the workbench
- 1MΩ resistor for each connection
- 2m earth wire with eyelet termination
- Supplied with fitting screws

RS PRO ESD Grounding

RS Stock No.: 0218650, 0218651, 0218653,
0218654, 0218656



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Buy this product from www.rspro.com

L Shaped under bench Earth Bonding Bracket with 4 different configurations available. It's yellow design ensures easy identification and it is supplied with fitting screws for secure installation.

General Specifications

Product Type	Noto Sans Med 10pt – RGB 95,98,95
Colour	Yellow
Resistivity	1 MΩ
Connection Type	Assorted – see below
Termination Type	Eyelet
Cord Length	2m

Approvals

Complies with EN 61340-5-1	Yes
Standards Met	ANSI/ESD S20.20

Similar Products

Stock No.	Brand	Product Name	Connection Type	Quantity
0218650	RS PRO	Earth Bonding Bracket	3 x 10mm stud	Each
0218651	RS PRO	Earth Bonding Bracket	3 x 4mm Banana	Each
0218653	RS PRO	Earth Bonding Bracket	1 x M5 Post	Each
0218654	RS PRO	Earth Bonding Bracket	2 x 4mm Banana + 1 x 10mm stud	Each
0218656	RS PRO	Earth Bonding Bracket	1 x 4mm Banana + 2 x 10mm stud	Each

