



Radial insert ball bearings RAE40-XL-NPP-B (Series RAE..-NPP-B)

spherical outer ring, location by eccentric locking collar, P
seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (<http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp>) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
DSF	80 mm
B ₁	43,8 mm
B	30,2 mm
C	21 mm
d ₂	49,4 mm
d ₃	58 mm
max	
S	11 mm
W	5 mm
m	0,63 kg Mass
C _{ur}	1010 N Fatigue limit load, radial
C _r	34500 N Basic dynamic load rating, radial
C _{0r}	19800 N Basic static load rating, radial
f ₀	14 Calculation factor

