

Datasheet

RS Pro GFHF Series 1A 250 V ac 400Hz Chassis Mount Power Line Filter, with Tab Terminals

RS Stock No: **239-876**



Product Details

RS Pro 1 A power line filter works with voltages up to 250V at 400Hz. This two-stage RFI filter has tab terminals. It is suitable for sensitive electronic equipment and applications with intensive and frequent interference. This filter provides high-level attenuation.

Features and Benefits

- Includes capacitor discharge resistor
- Electrical connections by 250 (1/4 Inch) size terminals suitable for soldering or push-on receptacle
- High attenuation

**Specifications:**

Mounting Type	Chassis Mount
Termination Style	Tab
Depth	76 mm
Dimensions	46 x 76 x 28 mm
Height	28 mm
Length	46 mm
Maximum Current Rating	1 A
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-25°C
Operating Frequency	400 Hz
Maximum Voltage Rating	250 V ac