



MASTERColour CDM-R111

MASTERColour CDM-R111 35W/830 GX8.5 24D 1CT

The MASTER Colour CDM-R111 combines the trendy look of the 111mm aluminium reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTER Colour CDM

Product data

• General Characteristics

Cap-Base	GX8.5
Bulb	R111 [R 111mm]
Bulb Finish	Reflector
Burning Position	any [Any/Universal]
Life to 5% failures EM	5000 hr
Life to 5% failures EL	6000 hr
Life to 10% failures EM	5500 hr
Life to 10% failures EL	7000 hr
Life to 20% failures EM	6000 hr
Life to 20% failures EL	9000 hr
Life to 50% failures EM	7500 hr
Life to 50% failures EL	12000 hr

• Light Technical Characteristics

Beam Description	Narrow Flood
Beam Angle	24 D
Technical Beam Angle	18 (min), 23 (nom), 28 (max) D
Luminous Intensity	7500 cd
Colour Code	830 [CCT of 3000K]
Colour Rendering Index	85 Ra8
Colour Designation	Warm white
Colour Temperature	3000 K
Technical	2900 K
Lamp Luminous Flux EL	1350 Lm

LLMF - end nominal lifetime	45 %
Chromaticity Coordinate X	0.440 -
Chromaticity Coordinate Y	0.399 -
Luminous flux in 90° cone	1300 Lm

• Electrical Characteristics

System Power EM	47 W
System Power EL	44 W
Lamp Wattage	35 W
Lamp Wattage EM	35 W
Lamp Wattage EM 25°C, Rated	38.0 W
Lamp Wattage EL	35 W
Lamp Wattage EL 25°C, Rated	39.0 W
Lamp Voltage	88 V
Lamp Current EM	0.53 A
Lamp Current EL	0.475 A
Ignition Time	30 (max) s
Run-up time 90%	3 (max) min
Re-ignition Time [min]	15 (max) min
Dimmable	no
Warm-up Time to 60% Light Outp	120 s

• Environmental Characteristics

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content	2.8 mg

MASTERColour CDM-R111

Energy consumption 43 kWh
kWh/1000h

• UV-related Characteristics

Damage Factor D/fc 0.2 (max) -
PET (NIOSH) 8 (min) h500lx

• Measuring Conditions

Switching cycle 1050X

• Product Dimensions

Overall Length C 95 (max) mm
Diameter D 111 (max) mm
Overall Length C 3.75 (max) in
[inch]

• Product Data


Order code 204509 10
Full product code 871150020450910
Full product name MASTERColour CDM-R111
35W/830 GX8.5 24D 1CT
Order product name MASTERC CDM-R111 35W/830
GX8.5 24D 1CT
Pieces per pack 1
Packing configuration 6
Packs per outerbox 6
Bar code on pack -
EAN1 8711500204509
Bar code on
outerbox - EAN3 8711500204516
Logistic code(s) -
12NC 928088305330
ILCOS code MRS/UB-35/830-H-GX8.5-111/88/24
Net weight per piece 0.096 kg

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing




GX8.5

MASTERColour CDM-R111 35W/830 GX8.5 24D 1CT

Product	C (Max)	D (Max)
CDM-R111 35W/830 24D	95	111

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, November 30
data subject to change