

## Product information

# 125MM ANGLE GRINDER



### 9558NB

Bore	22 mm
Spindle Size	M14x2mm
No load speed	11000 rpm
Max Wheel Diameter	125 mm
Input wattage	840 w
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound power	97 dB(A)
Noise sound pressure	86 dB(A)
Noise K factor	3 dB(A)
Net weight	1.5 kg
Vibration artificial wheel	8.5 m/sec <sup>2</sup>



- Compact & Lightweight .
- Ideal for general grinding & cutting applications.
- Lock-on switch to reduce user fatigue.
- Side handle for operator control.
- Higher motor power.

Details correct as of: 23-2-2012

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makitauk.com](http://www.makitauk.com)