

# Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel black



## fields of application

- Mechanical and system engineering
- Model construction
- Home technology



## description

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated

## technical data

### ➤ general

Bezel color	black
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	11 g
Operating life	150,000 cycles
B10	195,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

### direct links

- [RAFI eCatalog](#)

### ➤ mounting diameters

Outside dimension, length	20 mm
Outside dimension, width	20 mm
Outside dimension, height	50 mm
Mounting hole	16.2 mm
Mounting depth	41 mm
Installation height	9 mm

### ➤ mechanical data

Actuation function	momentary contact function
--------------------	----------------------------

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Feb 21, 2025 page: 1/3

### RAFI GmbH & Co. KG

Ravensburger Str. 128-134  
88276 Berg / Ravensburg  
Germany  
[www.rafi-group.com](http://www.rafi-group.com),  
[info.headquarters@rafi-group.com](mailto:info.headquarters@rafi-group.com)

Operating force, min.	7,5 N
Operating travel, max.	4.3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal

**> electrical data**

Rated voltage, max.	250 V
Rated current, max.	2 A

## drawings

### Dimensioned drawing

