

Add-on block 2P 25A 300mA AC

Technical Properties

Number of poles	2 P
Rated current	25 A
Rated residual operating current	300 mA
Residual current type	AC
Number of modules	2
Frequency	50 Hz
Rated operational voltage Ue	230/400 V
Operating temperature	-5 to 40 °C