

# TPS101

## Outdoor Single Gang Socket

### Features & Benefits

- 13 amp single gang socket
- 2 x earth terminals in back box for continuity
- IP55 weatherproof rating (when lid closed)
- Impact resistant housing
- Spring back socket lid cover
- Suitable for all BS 13 amp plugs



### Technical Data

|                                   |   |
|-----------------------------------|---|
| Operating Voltage                 | 230V AC   |
| Frequency                         | 50Hz  |
| Installation Type                 | Surface   |
| Earth Class Rating                | Class I   |
| Operating Temperature             | -10°C to 40°C                                   |
| Ingress Protection Rating         | IP55  |
| Socket Outlet                     | Single Gang 13A BS Plug                         |
| Mounting Hole Centres (mm)        | 55  |
| Cable Capacity (mm <sup>2</sup> ) | x3 2.5mm <sup>2</sup> Cables                    |
| Cable Entry(s)                    | Multiple M20 Knockouts, x1 Grommet Bottom Entry |

### General

# Data sheet

## TPS101

Safety / Powerseal Outdoor Power

|                   |                                  |
|-------------------|----------------------------------|
| Weight (g)        | 137.5                            |
| Height (mm)       | 85                               |
| Width (mm)        | 70                               |
| Depth (mm)        | 54                               |
| Body Construction | Polycarbonate (Impact Resistant) |
| Product Colour    | Grey                             |
| EAN Number        | 5012483009147                    |
| Guarantee Period  | 3 Years                          |

### Line Diagrams

