



A22NE-M-P202-N-B

E-Stop, push-in, 2NC, 40-dia. head Medium Turn-reset. with integrated control box

Specifications

Number of contacts, normally-open	0
Number of contacts, normally-closed	2
Unlocking method	Turn unlatching mechanism
Diameter cap	40 mm
Hole diameter	22 mm
Mounting method	Surface mounting
With lighting	×
With lock lever contact function	×
Button text	STOP
Text color	Black
Lighting voltage	Not Applicable
Connection type auxiliary circuit	Spring clamp connection
Degree of protection (IP)	IP65

CAD Library



A22NE Emergency Stop Push Button Switches Datasheet

EN PDF 20.4 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Innovation in Control Panel Building Brochure

EN PDF 4.38 MB



Machine Safety Catalogue

EN PDF 9.91 MB



Pushbutton Switches Brochure

EN PDF 2.78 MB



Safety Component Selection Guide EU Brochure

EN PDF 5.26 MB



Safety Solution Advanced Guide Guide

EN PDF 2.57 MB



Safety Solution Basic Guide Guide

EN PDF 14.4 MB