

Terminal, iPo plug-in terminal, PE/PEN terminal, 16 mm², green-yellow



Model	
product brand name	SENTRON
product designation	ALPHA FIX terminal blocks
design of the product	iPo through-type terminal
General technical data	
insulation material	thermoplastic
terminal contact spacing	12 mm
Protection class	
combustibility class according to UL 94	V0
Appearance	
color	miscellaneous
Product details	
product component required end cover plate	Yes
Number	
number of terminal levels	1
number of terminal points per terminal level	2
Connections	
stripped length	18 mm
connectable conductor cross-section solid	
• minimum	0.5 mm²
• maximum	25 mm²
connectable conductor cross-section stranded	
• minimum	25 mm²
• maximum	0.5 mm²
connectable conductor cross-section finely stranded	
• with core end processing minimum	0.5 mm²
• with core end processing maximum	16 mm²
• without core end processing minimum	0.5 mm²
• without core end processing maximum	25 mm²
type of connection 1	Miscellaneous
type of connection 2	Miscellaneous
position of the terminal	top
Mechanical Design	
height	75.4 mm
height with lowest-profile installation	60.1 mm
depth	52.63 mm
length	75 mm
fastening method	TH35 DIN rail
net weight	37 g
material of the insulating body	Other

Environmental conditions	
ambient temperature during operation	
• minimum	105 °C
• maximum	105 °C

Approvals Certificates		
General Product Approval	Declaration of Con- formity	other



[Confirmation](#)



[Confirmation](#)

other	Environment
-------	-------------

[Miscellaneous](#)

[Environmental Con-
firmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WH6000-0CK07>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WH6000-0CK07>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WH6000-0CK07

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

2/8/2023 

