



ENGLISH

Datasheet

Stock No: 243-5543

RS Pro Line Mounting Hydraulic Flow Control Valve, G 1/2, 350 bar



Product Details

High Pressure Flow Control

High pressure flow control valves for general purpose use in a hydraulic system.

Single and double acting versions available

Both ranges have an easy to read colour flow graduation scale and a locking screw to stabilise flow

Nitrile rubber seals

Temp. range -10 to +100°C

0.5 bar cracking pressure

Flow Control Valves

Single acting and double acting in-line flow control valves. Single acting valves allow flow control in one direction and free flow in the opposite direction. Double acting valves allow flow control in both directions.



ENGLISH

Specifications:

Manufacturer Series	NDV
Connection Port Thread	G 1/2
Maximum Flow Rate	140L/min
Body Material	Steel
Seal Material	Nitrile Rubber
Maximum Operating Pressure	350 bar
Thread Size	1/2 in
Thread Standard	G
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-10°C