

Signal lamp with lamp socket, BA 9s, 16.2 mm, IP40, housing, 250 Volt, Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated



fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Signalling systems
- Model construction

description

Signal lamps for LEDs or filament/neon lamps with BA 9 s socket, mounting hole diameter 16.2 mm

technical data

➤ general

illuminated	Yes
Lamp socket	BA9s
Packaging unit	10 pcs.
net weight	6.9 g
Degree of protection, front side, according to DIN EN 60529	IP40
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

- [RAFI eCatalog](#)

➤ mounting diameters

Outside dimension, length	20 mm
Outside dimension, width	20 mm
Outside dimension, height	60.8 mm
Mounting hole	16.2 mm
Mounting depth	45.8 mm
Installation height	15 mm
Collar dimension	20 mm

➤ mechanical data

Fixing	Threaded ring
Solderability	Yes

Terminal on the rear	Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated
> electrical data	
Operating voltage of the luminous element, max.	250 V

drawings

Mounting hole drawing

