



# RUBBERMAID ELITE 60L/15.9G STAINLESS STEEL STEP-ON BIN, DUAL STREAM

SKU: 2145985



## RUBBERMAID ELITE 60L/15.9G STAINLESS STEEL STEP-ON BIN, DUAL STREAM

The Rubbermaid Elite 60L Dual Stream Step-On Bin offers a streamlined waste and recycling solution for professional facilities. Equipped with colour-coded liners, it allows easy separation of waste and recycling without reducing capacity. The charcoal stainless-steel foot pedal ensures hands-free operation, while the quiet-close lid reduces unwanted noise. Its fingerprint-resistant finish maintains a professional appearance, making this bin a smart, low-maintenance option for workplaces, hotels, and healthcare facilities.



## FEATURES AND BENEFITS

- **STAINLESS STEEL CONSTRUCTION:** Sleek design and deep charcoal stainless-steel complements your facility.
- **WASTE AND RECYCLING SOLUTION:** Colour coded liners in black and blue allow for easy sortation of waste and recycling, without sacrificing waste capacity, and fit standard liners using bag cinch.
- **EASY TO MAINTAIN:** Finish naturally hides fingerprints, smudges and dirt.
- **SLOW CLOSE LID:** Quiet, controlled lid closure is designed to reduce unwanted noise by easing down gently.
- **HANDS-FREE USE:** The charcoal stainless-steel foot pedal stands up to daily use and removes the need to touch the lid during waste or recycling disposal to keep hands clean.



# RUBBERMAID ELITE 60L/15.9G STAINLESS STEEL STEP-ON BIN, DUAL STREAM

SKU: 2145985

## SPECIFICATIONS

	Metric	Imperial
Product Length	60.01 cm	23.63 in
Product Width	43.18 cm	17 in
Product Height	72.71 cm	28.63 in
Product Weight	4.08 kg	4.08 kg
UPC	71691534297	71691534297
Case Pack Length	60 cm	
Case Pack Width	43.18 cm	
Case Pack Height	72.7 cm	
Case Pack Weight	14.08 kg	
Capacity	60 L	
Country of Origin	China	China