



BE-8910i - BE-8925i

ERGO™ Stainless Steel TORX® Screwdrivers with 3-Component Handle T10-T25










PRODUCT DETAILS

- Screwdriver developed according to the scientific ERGO™ process
- ERGO™ stainless-steel screwdriver for TORX® head screws
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Flat face to prevent rolling
- Integrated hanging hole
- SS blade protects against formation of rust that can occur when screwdriving jobs on stainless-steel are performed with non-stainless-steel tools
- Easy to choose correct tip using colour-coded handle and permanent symbol on domed end
- Standards: ISO 8764, DIN 5260



PRODUCT ATTRIBUTES

Product							
BE-8910I	T 10	2.72 mm	75 mm	3 mm	20 mm	122 mm	197 mm
BE-8915I	T 15	3.26 mm	100 mm	4 mm	27 mm	122 mm	222 mm
BE-8920I	T 20	3.84 mm	100 mm	4 mm	27 mm	122 mm	222 mm
BE-8925I	T 25	4.40 mm	125 mm	5 mm	27 mm	122 mm	247 mm

Follow the Fish!

