



Main

Commercial Status	Commercialised
Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	130 mm
IP degree of protection	IP67 conforming to IEC 60529 IP66 conforming to IEC 60529
[Us] rated supply voltage	230 V AC
Light source	High luminosity LED, orange

Complementary

Material	PC (globe) ABS (acrylonitrile butadiene-styrene) (body part)
CAD overall width	130 mm
CAD overall depth	130 mm
Product weight	0.99 kg
Marking	CE
Product mounting	By 3 M6 screws
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	22 mA
Flashing frequency	2.7 Hz
Clamping connection capacity	1.25 mm ²
AWG gauge	18
Cable length	400 mm

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-30...50 °C
Class of protection against electric shock	Class II conforming to IEC 61140

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rotating Mirror Beacon

Dimensions



