



Datasheet

ENGLISH

RS Pro Process Indicator, 77 x 35mm Analogue Input, 230 V ac Supply Voltage ON/OFF

Stock No: 798-3501



3 YEAR
WARRANTY



Product Details

This Series of Digital Process Indicators are designed to be used in a wide variety of applications due to their ease of set-up

Typical applications include:

Transmission of pressure, humidity & temperature

Motor driver speed measurement

Shunt resistance current measurement

Professional range of easy-to-program Digital Process Indicators

24 & 240 V options available

Easily adjusted via the front panel

Selectable decimal point location

Customisable alarm output which can be set from the front panel of the Process Indicator

Specifications

Supply Voltage:	230 V ac
Size:	77 x 35mm
Minimum Operating Temperature:	0°C
Maximum Operating Temperature:	+50°C
Temperature Range:	0 → +50 °C
Control Type:	ON/OFF
Configurable Outputs:	Relay
Communication Module Available:	No
Display Type:	LED
IP Rating:	IP20, IP65
Panel Depth:	62.5mm
Input Type:	Analogue
Series:	RS Pro
Mounting Type:	DIN Rail
Display Colour:	Red