



6310DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6310DDUC3

Boundary Dimensions

d	50	mm	Bore diameter
D	110	mm	Outside diameter
B	27	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	68000	N	Basic dynamic load rating
C0r	38500	N	Basic static load rating

Speeds

Grease	4300	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	59	mm	Diameter of shaft abutment
da (max.)	68	mm	Diameter of shaft abutment
Da (max.)	101	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	13.2	Factor
----	------	--------

Additional information

z	8	Number of Balls	
Dw	19.05	mm	Ball Diameter

Mass

Mass approx.	1.06	kg	Mass approx.
--------------	------	----	--------------

