



Arms & Accessories

38mm x 1M Stainless Steel Flexible Arm Kit

	Capture Apparatus Included			
	Pen-nib nozzle (38mm ID) Max D x H 180 x 190mm			Clamped bench bracket
Conical cowl (95mm ID) Max D x H 190 x 200mm			51mm x 2m flexible hose 2 x Connecting cuffs 1 x Support collar and valve	
Code: 100295				

Capture Apparatus (Optional)							
Clear hood cowl (265 x 310mm) Code: 840160	Max W x L 300 x 200mm			Delta cowl (192 x 5mm inlet) Code: 840182	Max W x L 200 x 150mm		

100mm x 2M Flexible Arm

	Capture Pattern	
	Max D x H 300 x 300mm * Factory fit only. Must be ordered with a suitable machine.	
Code: 120175* Supplied with conical cowl and mounting bracket.		

Cleancab Enclosed Hood

		Includes: Base Open Hood 50mm Airflow valve
Code: 840150 Includes free 100043 connection kit	Depth = 510mm	