


4
DRAWING MADE IN THIRD ANGLE PROJECTION
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
G	14	ZONE	LTR	DESCRIPTION	DATE	APPD
			J	EC 0720-0279-93	6-21-93	BB

AMP
WIRE RANGE
2 AWG
STRANDED

METRIC
DIMENSIONS LISTED IN mm [INCHES]



1. TONGUE MATERIAL THK 1.45±0.08 [0.057±0.003]
FOR 11.89 [0.468] MAX WIRE INS DIA

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:
105°C

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
26.7-42.4mm² [52,600-83,700]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

M525036-126 CLASS 2	-	LOOSE PC	324053
MILITARY P/N AND CLASS	QTY	PACKAGE TYPE	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED	DR 6-21-93 S.S. GOULDEN	AMP AMP Incorporated Harrisburg, PA 17105-3608	
TOLERANCES ON: 2 PLC DEC ± 0.20 [0.008] 3 PLC DEC ± - ANGLES ± -	CHK 6-21-93 R. HERSEY	NAME	
MATERIAL COPPER PER ASTM B-152 NYLON OIL-M-20693) TYPE 1 COLOR: RED	APPD 6-21-93 B. BARE	TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 2 AWG	
FINISH TIN PLATE PER MIL-T-10727	APPD 6-21-93 M. ELLIS	SIZE	CAGE CODE
	PRODUCT SPEC	B	00779
	APPLICATION SPEC	DRAWING NO	C-324053
	WEIGHT -	SCALE	SHEET
		NTS	1 OF 1