

Power Tools

ProSet® XT3 - *The High Performer*

The ProSet XT3 can be used in a variety of applications, setting a large range of breakstem rivets, lockbolts and sealing plug sizes. The extremely large stroke of 26 mm allows the placement of longer rivets like Monobolt and Interlock in one set.

Specifications

Weight, incl. nose equipment	2.14 kg
Weight, without nose equipment	2.0 kg
Pull force at 5.5 bar	17.0 kN
Force/Weight ratio	7.94 kN/kg
Stroke (min.)	26 mm
Cycle time (approximate)	0.9 sec
Air supply pressure (dry, filtered)	5.0 - 7.0 bar
Free air volume at 5.5 bar	6.3 l
Noise level	78.4 dB(A)



ProSet® XT4

The ProSet® XT4 is the strongest tool of the ProSet family. With 23 kN, the XT4 delivers the highest pull force in the range but weighs in at just about 2 kg. As well as structural breakstem rivets, the high capacity of the XT4 also allows installation of Avdelok®, Maxlok®, and Avtainer® lockbolts.

Specifications

Weight, incl. nose equipment	2.16 kg
Weight, without nose equipment	2.0 kg
Pull force at 5.5 bar	23.0 kN
Force/Weight ratio	10.65 kN/kg
Stroke (min.)	18 mm
Cycle time (approximate)	1.0 sec
Air supply pressure (dry, filtered)	5.0 - 7.0 bar
Free air volume at 5.5 bar	6.3 l
Noise level	77.9 dB(A)

