


MARQUARDT

SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

single-pole 	Normally closed contact (SPNC)			Normally open contact (SPNO)			Switch (SPDT)							
	1801.63.25	1801.13.02	1801.13.03	1801.62.22	1801.12.02	1801.22.02	1803.11.21	1803.21.02	1803.24.02	1803.25.03	1803.51.02	1803.61.21	1803.61.52	
Voltage lamp in V														
Actuator color / printing	Black	Black	Red	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	
Housing color	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	
12 (4) A 250 V AC 1E4														
10 (4) A 250 V AC 1E4	•			•			•	•	•	•	•	•		
8 (8) A 250 V AC 5E4														
6 (4) A 250 V AC 5E4	•			•			•	•	•	•	•	•		
6 (2) A 250 V AC 1E4														
4 (3) A 250 V AC 6E3														
4 (2) A 250 V AC 1E4		•	•		•	•								
30 mA 12 V 5E4														
30 mA 12 V DC 5E4													•	
15 A 250 V AC 1 1/2 HP														
15 A 125 V AC 3/4 HP														
10 A 250 V AC 1/2 HP	•			•			•					•		
10 A 125 V AC 1/3 HP	•			•			•					•		
6 A 250 V AC 1/2 HP								•	•	•	•			
6 A 125 V AC 1/4 HP								•	•	•	•			
6 A 125 - 250 V AC 1/8 HP														
6 A 125 V AC 1/10 HP		•	•		•	•								
4 A 250 V AC 1/10 HP		•	•		•	•								
Connection type	U	U	U	U	U	U	U	U	U	U	J	U	U	
Connection description		4.8	4.8		4.8		4.8							
Inrush current in A (capacitive)														
Contact distance in mm	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	
Contact material	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	
EN 60335 cap. 30 conform *G*														
Miscellaneous									Installation depth 13.2	Installation depth 16.2				
Stock version		•		•	•	•	•	•	•		•	•	•	