



GBC CombBind® CB15 Manual Binding Machine

The CombBind® CB15 is a reliable and compact manual comb binder, perfect for personal or small office use with low volume needs. It effortlessly punches through up to 15 sheets of 80gsm paper and can bind up to 165 sheets at a time using 19mm spines. Its lightweight, space-saving design ensures it can be used anywhere, anytime, and easily stored when not in use. For added convenience, it includes a clippings tray for easy disposal and a handy storage compartment. Black and silver colour.



Attributes

- Binds up to 165 A5/A4 sheets (80gsm) at a time using a 19mm comb.
- Punches up to 15 sheets at a time (80gsm)
- Versatile binding: easily bind A5 documents with A5 combs and A4 portrait pages with A4 combs.
- Manual double-handle punch for a smooth binding experience with minimal effort.
- Side margin adjustment for precise alignment and consistent binding results.
- Fixed margin depth for consistent and high quality binding.
- Non-slip rubber feet for stable and secure placement.
- Convenient clippings tray and a built-in storage compartment for added organisation.
- Lightweight and compact design for easy portability and convenient storage.

Specifications

Number	4410061
Colour	black
Material	Plastic
Dimensions (W x H x D)	458 x 295 x 264 mm
For Format	A4/A5
Max. Binding Width (mm)	297
Operation Mode	Manual Double Handle
Max. Binding Capacity (70gsm paper)	165
Punch Capacity (70gsm paper)	17
Punch Capacity (80gsm paper)	15
Punch Capacity (Clear Film 0,2 mm)	2
No. of Punches	21
Electric punching	No
Spine size selector	No
Max. Comb Diameter (mm)	19
Waste tray	Yes
Suitable for	Comb Punch and Bind
Weight	4600 g
Packing unit	1
Pallet quantity	0
Minimum order quantity	1
EAN code	5028252644464