



Cut



Medium Duty

## Abrasion-resistant gloves, with color coding to ensure appropriate application

- **Indicated protection levels:** HyFlex® 11-425 industrial gloves follow a color-coded indicator system, helping workers identify when to use them safely
- **Prolonged durability:** HyFlex® 11-425 industrial safety gloves meet ANSI/ISEA 105-2024 ABRASION LEVEL 6 and EN ABRASION LEVEL 4 standards
- **Added grip and eco-friendliness:** The HyFlex® 11-425's PU and nitrile coating provides strong grip and is water-based, for a more environmentally friendly fabrication process
- **Advanced defences and comfort:** INTERCEPT™ Cut Resistance Technology fibres are seamlessly knitted to meet ANSI/ISEA 105-2024 CUT A3 and EN ISO C standards, offering greater comfort
- **Guaranteed convenience:** These industrial gloves are available in vend pack form, facilitating rapid access
- **Certified skin-friendliness:** Dermatest® certification ensures these PPE gloves are skin-friendly



### Industries

- Automotive
- Chemical
- Food Processing

### Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Applying sealers, touching up
- Production line support & maintenance
- Loading and unloading trucks and vehicles
- Product shipping, transport and delivery
- Maintenance
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Lock smith

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-425

Designed to make the selection of hand protection easy

Previously known as: Puretough™P5000

### Key Features

- **HyFlex® indicator system:** Workers can ensure adequate protection
- **Certified abrasion resistance:** Excellent durability
- **Water-based PU and nitrile coating:** Enhanced grip and comfort

### Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Technologies



DMF free



**INTERCEPT™**  
Cut Resistance Technology

### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                                                                           | Gauge | SIZE               | LENGTH                        | COATING COLOR | PACKAGE                      |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-------------------------------|---------------|------------------------------|
| HyFlex® 11-425 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Water-Based polyurethane and nitrile<br><b>Liner Material:</b> Polyamide, Fiber glass, HPPE<br><b>Cuff Style:</b> Knitwrist | 13    | 6, 7, 8, 9, 10, 11 | 225-270 mm; 8.86-10.62 inches | Grey          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**