



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2083075-2
C/A Nector S Plug to Pigtail LV-2 SVT
Wh

TE Part # 1-2083075-1
Cable assy Nector S female to

TE Part # 2-2083075-1
C/A Nector S Plug to Pigtail LV-2 SVT
Wh

Customers Also Bought

TE Part #61045-2
FASTON .187 SERIES (4.8 MM) TPBR

TE Part #34144
PG R 22-16 COMM 22-18 MIL 6

TE Part #1-2834067-2
SOCKET CONTACT,MINIATURE
WATERPROOF CONN

TE Part #152873
14-12 PIDG NYLON RT NO 8 WHITE

TE Part #293284-1
NECTOR S BUS BAR BOOT

TE Part #2213211-1
NECTOR S BUS BAR BOOT US

TE Part #1-1609112-3
15CBS1=F8273

TE Part #34146
PG R 22-16 COMM 22-18 MIL 10

TE Part #61765-1
FASTON ADAPTER .250 RECEPTACLE
BR

TE Part #1-2083075-1
Cable assy Nector S female to

Documents

Product Drawings

Cable assy Nector S female to pigtail,UL

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-2083075-2_E1.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_1-2083075-2_E1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2083075-2_E1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English