

Plunger(针轴):BeCu Rh Plated

Sping(弹簧):SUS304 Not Plated

Barrel(内管):Brass Au Plated

最小中心距 (Min. Center):1.9mm [0.0748]

最大行程 (Full Stroke): 3.35mm [0.1319]

2.54mm [0.10]

行程全压弹力 (Full Stroke Spring Force): ±20%

128g [4.52oz]

2/3行程弹力 (2/3 Stroke Spring Force): ±20%

90g [3.18oz]

额定电流 (Current Rating):3A


接触电阻 (Contact Resistance):30mΩ

建议钻孔尺寸 (Recommended Hole Size)

亚克力 (Acrylic):1.35mm [0.0531]

电木板 (Bakelite):1.40mm [0.0551]

玻璃纤维板 (Fiber Reinforce Plastic):1.40mm [0.0551]



变更记录 CHANGE RECORD	△					
	△					
	△					
	序号 NO.	变更内容 MODIFY CONTENT	变更者 WRITER	审核 CHECKED	日期 DATE	
品名 DESCRIPTION	探针	版本 VERSION	A	日期 DATE	2008.8.26	
机种 MODEL NO.	2615187	制图 DRAWING	Caigangfeng			
料号 PART NO.	P-1E2-0613	公差 TOLERANCE	±0.1	比例 SCALE		审核 CHECKED
图号 DRAWING NO.	FCT008	第三角法 3RD ANGLE	单位 UNIT	MM	批准 APPROVED	Du menghe