


suction cup holder ESH-HCL-6-G

Part number: 189232

FESTO

with increased height compensator, vacuum connection at top,
compensator secured by two hexagonal nuts.



Data sheet

| Feature | Value |
|---|--|
| Height compensator for suction-cup holder | 40 mm |
| Volume | 16.325 cm ³ |
| Assembly position | Vertical |
| Design structure | Vacuum connection at top with height compensation |
| Correlation to suction-cup holder | Size 6 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 560 g |
| Mounting type | with lock nut |
| suction cup mounting | M20x2 |
| Vacuum connection | G1/4 |
| Materials note | Conforms to RoHS |
| Material bracket | POM Heat-treatment steel High alloy steel |