



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater with fan
Range compatibility	Prisma P Prisma G
Power range	250 W
Input voltage	230 V AC 50/60 Hz

### Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	UL VDE
Material	Extruded aluminium for body
Height	200 mm
Width	100 mm
Depth	100 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

### Contractual warranty

Warranty period	18 months
-----------------	-----------