

Datasheet

RS Pro 3 Pole Non-Fused Switch Disconnecter, 40 A, IP54

RS Stock No: **773-8014**



Product Details

RS Pro 3-pole non-fused switch disconnecter has a current rating of 40 A. It is constructed from flame retardant ABS for long life durability. This IP54 rated unit is easy to access and has interlocking lid that ensures removal in the off position. It is suitable for use with low voltage switchgear such as power distribution, load isolation and motor start/stop. The switch disconnecter meets EN60947 standards.

Features and Benefits

- Interlocking lid ensures removal in the OFF position only
- Easy access and switch removal
- Padlockable handles
- Flame retardant material

**Specifications:**

| | |
|-------------------------------|-----------------------|
| Accepts Padlocks | Yes |
| Auxiliary Contacts Available | Yes |
| Depth | 74 mm |
| Electrical Phase | 3 |
| Handle Colour | Red |
| IP Rating | IP54 |
| Length | 125 mm |
| Maximum Current | 40 A |
| Maximum Operating Temperature | +40°C |
| Minimum Operating Temperature | -25°C |
| Mounting Type | Panel Mount |
| Number of Poles | 3 |
| Switch Rating | 30 kA |
| Voltage Rating | 690 V ac |
| Width | 145 mm |
| Cable Capacity | 10 mm ² |
| Material | ABS Plastic Enclosure |
| Standards Met | EN 60947 |
| Tightening Torque | 1.7 Nm |