

512N, E512N "N" Series Cutters

- Medium oval head, semi-flush



Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Dimension "B"		Dimension "C"		Shelf Pack	
			Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm		
RS 270-8475	512N	043127132025	Boxed	4.5	114	.063	1.6	.394	10	.256	6.5	.394	10	1
	512NV	043127144264	Carded	4.5	114	.063	1.6	.394	10	.256	6.5	.394	10	1
	*E512N	043127132148	Boxed	5.75	147	.063	1.6	.394	10	.256	6.5	.394	10	1

522N, E522N "N" Series Cutters

- Medium oval head, full flush



Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Dimension "B"		Dimension "C"		Shelf Pack	
			Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm		
RS 270-8481	522N	043127132032	Boxed	4.5	114	.063	1.6	.453	11.5	.256	6.5	.453	11.5	1
	522NV	043127144295	Carded	4.5	114	.063	1.6	.453	11.5	.256	6.5	.453	11.5	1
	*E522N	043127132131	Boxed	5.75	147	.063	1.6	.453	11.5	.256	6.5	.453	11.5	1

532N, E532N "N" Series Cutters

- Medium oval head, super full flush



Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Shelf Pack	
			Inch	mm	Inch	mm	Inch	mm		
	532N	043127137020	Boxed	4.5	114	.063	1.6	.394	10	1
	532NV	043127144301	Carded	4.5	114	.063	1.6	.394	10	6
	*E532N	043127137037	Boxed	5.75	147	.063	1.6	.394	10	1

* Ergonomic version