

Monitorarm

00116227 FULLMOTION Monitor Arm, VESA 100x100, 66 cm (26"), pneumatic spring, black

Highlightstext:

- For installing TFT/LCD/LED monitors with a screen size of up to 66 cm (26")
- Cable manager provides organisation and necessary strain relief
- Integrated high-performance pneumatic spring for continuous vertical orientation
- Can be swivelled up to 180°, tilted +/-90° and rotated 360°
- Supports all VESA standards up to 100x100
- Attachment to a table either with a clamping screw (tabletop thickness up to 10 cm) or drill mounting



Note for Consumers:

A minimum load of approx. 1.5 kg is required to ensure the holder is height-adjustable.

Technical Details:

- Maximum Load: 5 kg
- Model: Monitor Arm
- Monitor Fixation Standard: VESA incl. Adapter Plate
- Rotation Range: 360 °
- Tilt +/-: 90 / 90 °
- Adjustable Distance: Yes
- Max. Monitor Size: 66 cm
- VESA Standard: 100 x 100 mm/75 x 75 mm
- Width x Depth x Height: 11,5 x 52,2 x 11,2 cm
- Colour: Black
- For Monitors: 66 cm
- For a Table Top Thickness of: 10 cm

Scope Of Delivery:

- 1 FULLMOTION monitor arm
- Mounting hardware
- Assembly instructions

	Brand	Item-no.	VE
	hama [®]	00116227	4