

EAN: 4895251601603

ECOFLOW

RIVER 2 Pro

768Wh | 800W AC Output



Capacity
768Wh

Charging Power
940W (X-Stream)

Battery Chemistry
LFP

Normal charging time
70 Min

Cycle life
3000 cycles to 80% capacity

Dimension
270 x 260 x 226 mm

AC Output
800W (Surge 1600W)

Solar panel charging
11-50V, 13A, 220W Max

AC Output Ports
3

Connectivity
Wi-Fi & Bluetooth

Number of Outports
10

Net weight
Approx. 17.2 lbs / 7.8 kg

Power 80% of high-wattage home appliances



LED Light
23.7 hrs



Electric drill
46 mins



Cutting machine
46 mins



Circular Saw
46 mins



Electric hammer
46 mins

*The data provided is for reference only. Perform tests to verify the actual uptime of the device.