



WX3 HOLSTER TROUSERS

DESCRIPTION

Contemporary work trouser featuring clever holster pockets for ample storage and security. Made from durable poly-cotton canvas fabric and includes triple stitched seams, these trousers have a multitude of practical features including two-tier knee pad pockets, a high rise back waistband and an adjustable leg hem for added convenience. Innovative stretch panelling provides excellent comfort and flexibility in key movement areas.

COMPOSITION

-  **Titanmill Plus Canvas: 65% Polyester, 35% Cotton Canvas Peach Finish, 245g**
-  **87% Nylon, 13% Elastane, 245g**
-  **Olive Green 28-48**

FEATURES

- Durable soft polycotton canvas for high performance and maximum wearer comfort
- Innovative stretch panelling in key movement areas provides excellent comfort and flexibility
- Gripper elasticated inner waistline helping keep upper body garments in place
- Triple-stitched seams for extra durability
- Swing away tool pockets
- Two tier knee pad pockets allowing two positioning options
- 12 Pockets for ample storage
- 2 Side pockets
- Bottom loading knee pad pockets
- 1 Rule pocket
- 1 ID card holder
- 2 side zip pockets for secure storage

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T702OGR	OLIVE GREEN	28-14

FEATURES



STRETCH PANELS
Innovative stretch panelling in key movement areas provides excellent comfort and flexibility



BOTTOM LOADING KNEE PAD POCKETS
Knee pad pockets to facilitate knee pads



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



TECHNICAL STRONG WORKWEAR

Technical Strong Workwear built with innovative fabrics that will make your work day more comfortable.

GET THE COLLECTION



TECHINCAL INFORMATION



· Wash garment inside out and fully fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T702OGR28	Olive Green	65	45	36	1.068	5850.000	5036108354207	15036108842749
T702OGR30	Olive Green						FALSE	
T702OGR32	Olive Green	65	45	36	1.085	5850.000	5036108354221	15036108842763
T702OGR33	Olive Green	65	45	36	1.097	5850.000	5036108354238	15036108842770
T702OGR34	Olive Green	65	45	36	1.126	5850.000	5036108354245	15036108842787
T702OGR36	Olive Green	65	45	36	1.135	5850.000	5036108354252	15036108842794
T702OGR38	Olive Green	65	45	36	1.153	5850.000	5036108354269	15036108842800
T702OGR40	Olive Green	65	45	36	1.165	5850.000	5036108354276	15036108842817
T702OGR41	Olive Green	65	45	36	1.171	5850.000	5036108354283	15036108842824
T702OGR42	Olive Green	65	45	36	1.193	5850.000	5036108354290	15036108842831
T702OGR44	Olive Green	65	45	36	1.210	5850.000	5036108354306	15036108842848
T702OGR46	Olive Green	65	45	36	1.230	5850.000	5036108354313	15036108842855
T702OGR48	Olive Green	65	45	36	1.235	5850.000	5036108354320	15036108842862