


FEATURES

- Insulated hot junction for reduced electrical interference
- Miniature plug
- Termination for a quick and easy connection
- 310 stainless steel probe sheath for resistance to corrosion and oxidation

RS PRO Type K Thermocouple 150mm Length, 1mm Diameter → +750°C

RS Stock No.: 787-7762



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Thermocouples



Product Description

These thermocouple temperature probes have a durable construction and feature a 310 stainless steel mineral insulated flexible sheath that can be bent and formed to suit a wide range of applications. The thermocouple has a single element insulated junction for a reduction in electrical interference. One end of the thermocouple is terminated with a miniature flat pin plug for a quick and easy connection

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-40°C to 750°C
Construction	Flexible mineral insulated probe with 310 stainless steel sheath
Measuring Junction	Ungrounded
Application	heat exchangers, power stations, brick and cement kilns, heat treatment and annealing furnaces, thermostats, food thermometers, vehicle diagnostics and in laboratories

Mechanical Specifications

Probe Diameter	1mm
Probe Length	150mm
Probe Body Material	Stainless Steel
Insulation / Sheath Material	310 Stainless Steel

Approvals

Standards Met	IEC
---------------	-----



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensatin	ng:					
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Extension	on:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640



T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'K' 'K' 'K' 'K'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Green Green Green Green	White White White White	70643600	363-0250 110-4482 123-6306 123-6307
')' ')' ')'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Black Black Black Black	White White White	70643599	363-0244 123-6308 123-6309 123-6310
'T' 'T' 'T' 'T'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Brown Brown Brown	White White White White	70643601	363-0266 123-6311 123-6312 123-6313

T/C Type KX KX KX KX	Conductors 1/0.2mm 1/0.2mm 1/0.2mm	Cores +Yellow/-Red +Yellow/-Red +Yellow/-Red	Reel Length 25 metres 50 metres 100 metres	Allied code 70656106 70656111 70656109	RS order code 814-0030 814-0049 814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

Thermocouples



	Conductors	Cores		Jacket	Reel Length	Allied Code	RS order code
Exten	sion:						
KX	7/0.2mm	+Green/-	White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-	White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-	White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-	White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-	White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-\	White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-\	White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-\	White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-\	White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-\	White	Black	200 metres	70657081	827-5606
TX	7/0.2mm	+Brown/	-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/	-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/	-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/	-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/	-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-W		Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-W		Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-W		Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-W	/hite	Pink	100 metres	70657092	827-5640
T/C T	ype Co	nductors	Cores		Reel Length	Allied code	RS order cod
J	1/0	0.2mm	+Black/	-White	25 metres	70657194	827-5980
J	1/0	0.2mm	+Black/	-White	50 metres	70657195	827-5984
1	1/0	0.315mm	+Black/	-White	25 metres	70657198	827-5993

Conductors	Cores	Reel Length	Allied code	RS order code
1/0.2mm	+Black/-White	25 metres	70657194	827-5980
1/0.2mm	+Black/-White	50 metres	70657195	827-5984
1/0.315mm	+Black/-White	25 metres	70657198	827-5993
1/0.315mm	+Black/-White	50 metres	70657199	827-5996
1/0.315mm	+Green/-White	25 metres	70657200	827-6000
1/0.315mm	+Green/-White	50 metres	70657205	827-6019
1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
1/0.508mm	+Black/-White	25 metres	70657197	827-5990
1/0.508mm	+Black/-White	50 metres	70657201	827-6003
1/0.508mm	+Green/-White	25 metres	70657203	827-6012
1/0.508mm	+Green/-White	50 metres	70657204	827-6016
7/0.2mm	+Black/-White	25 metres	70657202	827-6006
7/0.2mm	+Green/-White	25 metres	70657207	827-6025
7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
7/0.2mm	+Pink/-White	25 metres	70657210	827-6034
	1/0.2mm 1/0.2mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.508mm 1/0.508mm 1/0.508mm 1/0.508mm 1/0.508mm 1/0.508mm	1/0.2mm +Black/-White 1/0.315mm +Black/-White 1/0.315mm +Black/-White 1/0.315mm +Green/-White 1/0.315mm +Green/-White 1/0.315mm +Brown/-White 1/0.315mm +Brown/-White 1/0.508mm +Black/-White 1/0.508mm +Green/-White 1/0.508mm +Green/-White 1/0.508mm +Green/-White 1/0.508mm +Green/-White 1/0.2mm +Black/-White 1/0.2mm +Black/-White 1/0.2mm +Black/-White	1/0.2mm +Black/-White 25 metres 1/0.2mm +Black/-White 50 metres 1/0.315mm +Black/-White 25 metres 1/0.315mm +Black/-White 50 metres 1/0.315mm +Green/-White 50 metres 1/0.315mm +Brown/-White 25 metres 1/0.315mm +Brown/-White 50 metres 1/0.315mm +Brown/-White 50 metres 1/0.508mm +Black/-White 50 metres 1/0.508mm +Green/-White 25 metres 1/0.508mm +Green/-White 50 metres 7/0.2mm +Black/-White 25 metres 7/0.2mm +Black/-White 25 metres 7/0.2mm +Brown/-White 25 metres 7/0.2mm +Brown/-White 25 metres	1/0.2mm +Black/-White 25 metres 70657194 1/0.2mm +Black/-White 50 metres 70657195 1/0.315mm +Black/-White 25 metres 70657198 1/0.315mm +Black/-White 50 metres 70657199 1/0.315mm +Green/-White 25 metres 70657200 1/0.315mm +Green/-White 50 metres 70657205 1/0.315mm +Brown/-White 25 metres 70657208 1/0.315mm +Brown/-White 50 metres 70657208 1/0.315mm +Brown/-White 50 metres 70657208 1/0.508mm +Black/-White 50 metres 70657201 1/0.508mm +Black/-White 50 metres 70657201 1/0.508mm +Green/-White 25 metres 70657204 7/0.2mm +Black/-White 25 metres 70657202 7/0.2mm +Black/-White 25 metres 70657207 7/0.2mm +Brown/-White 25 metres 70657207