

### Model 300 TH, N·m/lbf·ft



Norbar 16mm spigot torque handles can be used with a variety of spanner end fittings for versatility.

**Part number:** 15065

**EAN Bar Code:** 5060207564731

**NATO number:** -

**Accuracy:** +/-3%

**Operates between:**

**60.0 - 300.0 N·m**

**45.0 - 220.0 lbf·ft**



### TECHNICAL SPECIFICATIONS

- Length: 569 mm
- Weight: 1.17 Kg
- Packed Length: 730 mm
- Packed Weight: 1.92 Kg

### FEATURES

- Factory calibrated to  $\pm 3\%$  and our new mechanism ensures that the accuracy is retained for longer.
- Every wrench is supplied with a calibration certificate
- Ergonomic new handle with a high proportion of soft-feel, high grip material.
- Handle material and lens resist all chemicals in common automotive, industrial and aviation use.
- Secure push/pull locking mechanism is quick and intuitive to use and prevents accidental adjustment.
- Large scale window and long scale length for great visibility and accurate setting.
- Unique on a torque wrench, the TimeStrip<sup>®</sup> gives a visual indication that the wrench is due for re-calibration.