



560

E0893009.

TAP CONNECTOR, SELF STRIPPING BLUE, 0.75-1.5mm2 (AWG 18-14)



Product Properties:

Model	Branch
Colour insulation	Blue
Grease filling against corrosion	No
Max. number of cores	2 .
Temperature	-40-90 °C
Interrupt free shifting	Yes
Colour	Blue
Material insulation	Polypropylene (PP)
Connector type	Spliceing connector

Dimensions:

Core diameter	1-1.6 mm
Max. outer diameter	3.7 mm
MOQ	100 .
Unit	pcs
Nominal cross section	0.75-1.5 mm²

Approvals:

Approved according to CSA	Yes
With approval according to UL	Yes

Compliance:

Conflict Minerals	Yes, see report under tab "Documents"
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (241 Subs. 27 June 2024)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC000306 - Low current connector
ETIM-Release	9.0
Trademark	3M
Product Group	Self stripping tap connectors
Alternative SKU	560
E-no	E0893009.

Logistic information:

Barcode	054007200901
Country of origin	US
E-no	E0893009.
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	560
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

