

Shrink sleeve - WMS 2,4 (30X4)RL - 0800386

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Perforated, Mounting type: Slide on, Cable diameter: 0.8-2.4 mm, Lettering field: 30 x 4 mm



The illustration shows WMS 6,4 (30X10)R

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 626538
Weight per Piece (excluding packing)	480.5 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	30 mm
Width (a)	4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	white
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2000
Number of individual labels per row	2

Classifications

eCl@ss

eCl@ss 4.0	24190219
------------	----------

Shrink sleeve - WMS 2,4 (30X4)RL - 0800386

Classifications

eCl@ss

eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

Printing system accessories

Shrink sleeve - WMS 2,4 (30X4)RL - 0800386

Accessories

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm