



# 3/8 Drive 32 pc Ratchet + Socket Set Metric

## RATCHET AND SOCKET SETS

- 90 tooth design with 4 °of arc swing for tight work spaces.
- Comes with a removable inner tray perfectly designed to be stored.
- Sockets are stamped with measurements on the flat side for easy-to-read visibility.
- All metal design for maximum durability.
- FOUR FLAT™ sides on socket deter rolling.
- Slim profile head with flush direction lever offers better accessibility.



|                 |                                                                                                                                                                                                                                  |
|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Fits MILWAUKEE® | hexagon                                                                                                                                                                                                                          |
| Article Number  | 4932464945                                                                                                                                                                                                                       |
| Contents        | Standard sockets: 6 mm, 7 mm, 8 mm, 9 mm, 10 mm, 11 mm, 12 mm, 13 mm, 14 mm, 15 mm, 16 mm, 17 mm, 18 mm, 19 mm / Deep well sockets: 6 mm, 7 mm, 8 mm, 9 mm, 10 mm, 11 mm, 12 mm, 13 mm, 14 mm, 15 mm, 16 mm, 17 mm, 18 mm, 19 mm |
| Pack quantity   | 32                                                                                                                                                                                                                               |
| Quantity        | 1                                                                                                                                                                                                                                |