



Part Number : [397000304](#)
Product Description : 10.00mm Pitch, Eurostyle
Fixed-Mount Push-Button Terminal Block, 45° Modular
Luminaire, 10A, 26-14 AWG, Light Gray, 4 Circuits
Series Number : 39700
Status : Active
Product Category : Terminal Blocks and Barrier
Strip
Engineering Number : M240-00-7-04-M2



Documents & Resources

Drawings

[397000304_sd.pdf](#)

3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39700
Description	10.00mm Pitch, Eurostyle Fixed-Mount Push-Button Terminal Block, 45° Modular Luminaire, 10A, 26-14 AWG, Light Gray, 4 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	78172542232

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Gray (Light)
Entry Angle	45° Angle
Lock to Mating Part	None
Material - Plating Termination	Tin

Material - Resin	Nylon
Net Weight	0.007/kg
Number of Rows	1
Orientation	45° Angle
Panel Mount	Yes
Pitch - Mating Interface	10.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	14, 16, 18, 20, 22, 24, 26

This document was generated on Aug 04, 2025