



**Specifications:**

Contact rating: 650mA, 30V DC  
 Contact resistance: 20mOhm max.  
 Insulation resistance: 500MOhm min. at 500V DC  
 Dielectric strength: 500V, 50Hz for the duration of 1 minute  
 Operating temperature: -20°C to +60°C  
 Mechanical life: min. 20 000 cycles  
 Soldering conditions: hand-soldering: max.: 260 +/-5°C, 3sec.  
 Mounting: single-hole  
 Button color: red  
 Contact arrangement: off - mom  
 Material: phenolformaldehyde, black  
 Contacts: brass, silver plated  
 Terminals: solder tags



Tolerances:	Date	Name	<b>MSP 101 C</b>	Page
	11/08	dr		
			<b>knitter-switch</b>	<b>20 09 06</b>
Modifications	Date	Name		1/1