


E40612



Process adapters clamp DIN 32676 series C (ASME BPE)

ADAPT DIN32676-C DN40



Application	
Design	for volumetric flow meters SMF
Application	food and beverage industry; hygienic systems
Pressure rating	25 bar / 2.5 MPa
Tests / approvals	
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.
Mechanical data	
Weight [g]	2399.4
Materials	stainless steel (316L/1.4404)
Nominal diameter	DN40 (1 1/2")

E40612



Process adapters clamp DIN 32676 series C (ASME BPE)

ADAPT DIN32676-C DN40

Sensor connection	ifm-specific device flange
Process connection	Clamp DIN 32676 series C (ASME BPE)
Process connection suitable for pipe standard	(DIN EN 10357 series C); (DIN 11866 series C); (BS 4825 Part 1); (ISO 2037)
Surface characteristics Ra/Rz of the wetted parts	$Ra \leq 0.4 \mu m$
Accessories	
Items supplied	screws 8
Remarks	
Pack quantity	2 pcs.