



# 16G / 20° / 32 mm / G / SC1 - 2.000 pc

## FINISH NAILS, 16 GAUGE, 20°, THIN FINISH HEAD

- Suitable for M18 CN16GA, M18 FN16GA
- Collated angled strip



|                                        |                                                                                                                   |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------|
| Fits MILWAUKEE®                        | Brad nails for M18CN16GA                                                                                          |
| Article Number                         | 4932492582                                                                                                        |
| Dimensions (mm)                        | 1.35 x 1.61                                                                                                       |
| Head dimensions [mm]                   | 2.8                                                                                                               |
| Material                               | Galvanised                                                                                                        |
| Nail angle (°)                         | 20°                                                                                                               |
| Nailers and Staplers<br>[Configurator] | Milwaukee - M18<br>FN16GA;Paslode - IM65A<br>Angled Brad Nailer;Hikoki -<br>NT65GB;Dewalt -<br>DCN660;Bosch - GNH |
| Pack quantity                          | 2,000                                                                                                             |
| Service class                          | 1                                                                                                                 |
| Total length (mm)                      | 32                                                                                                                |