



Part Number : [1300680099](#)
Product Description : BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Black
Series Number : 130068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Number : TC40C40-200G



Documents & Resources

Drawings
[1300680099_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130068
Description	BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Black
IP Rating	IP67
Product Name	BradPower D-Size
Type	Power Tap Tee
UPC	78172536310

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	BradPower D-Size (1 3/8"-M35)
Drop Gender	Female
Keyway	Single
Left Trunk Connector	BradPower D-Size (1 3/8"-M35)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	458.000/g

Poles	4
Right Trunk Connector	BradPower D-Size (1 3/8"-M35)
Right Trunk Gender	Male
Temperature Range - Operating	-20°C to +90°C