

Telescopic Pole Saw XGT®

UA004G

40Vmax • 20 m/s • 30 cm / 12"

Powerful Telescopic Pole Saw XGT® with high chain speed for demanding applications.

XGT® Battery powered Telescopic Pole Saw; has high power, Brushless motor which delivers the same or higher operation efficiency than 35 cm³ class petrol engine models.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	20,0 m/s
chain bar length	300 mm (12")
Chain Pitch	3/8 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	46
Chain Oil Tank	160 ml
Brushless Motor	✓
Vibration Level (3 axes) at Rear Handle	3,1 m/s ²
Vibration Level (3 axes) at Front Handle	2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Sound Pressure Level (L _{pA})	90 dB(A)
Sound Power Level (L _{WA})	105 dB(A)

User benefits

- Lightweight pole saw head for easy access to a desired cutting position
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Battery protection system automatically shuts off power when the battery level is low
- Captive nuts to prevent loss of nuts when replacing guide bar or saw chain

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing