



Connectors > Automotive, Truck, Bus, & Off-Road Connectors > Connector Accessories > Other Connector Accessories > HDSCS FIXING SLIDES



Material: **PBT GF**
Color: **Violet**
Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

All HDSCS Fixing Slides (21)

Features

Body Features

Material	PBT GF
Color	Violet

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)



	Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Model / Part # CAT-H3399-CH8172
HDSCS HOUSINGS




TE Model / Part # 2-1564536-1
4POS,TAB5.8X0.8,
TABHSG,ASSY, COD. B


Also in the Series | HDSCS




Automotive Connector Caps & Covers(19)



Automotive Seals & Cavity Plugs(1)











Automotive, Truck, Bus, & Off-Road Housings(189)



Other Automotive Connector Accessories(22)



Customers Also Bought

 <p>TE Model / Part #1-1801178-6 3W RECEPTACLE HP CONNECTOR BROWN</p>	 <p>TE Model / Part #1-318088-2 ANVIL,SPECIAL COMBINATION</p>	 <p>TE Model / Part #1333208-2 ANVIL, COMBINATION (.120)</p>	 <p>TE Model / Part #1801178-6 3W RECEPTACLE HP CONNECTOR BROWN</p>
 <p>TE Model / Part #3-458141-9 CRIMPER, WIRE</p>	 <p>TE Model / Part #5052996041 RNF-100-1/8-0-30MM</p>	 <p>TE Model / Part #8953152001 RPPM-12/3-X-STK</p>	 <p>TE Model / Part #CH32556001 RPPM-NR510-X-80MM</p>

Documents

Product Drawings
SLIDE, TAB HSG GROUP E
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1564411-7_K.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1564411-7_K.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1564411-7_K.3d_stp.zip
English

Datasheets & Catalog Pages
HDSCS Catalog
English

Product Specifications
Application Specification
English