

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and longevity.
- **Flanged Design:** Ensures secure positioning and simplifies installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Compact Size:** With an outside diameter of 0.56 in, it fits into tight spaces.

RS PRO 0.31 in Plain Bearing, Sintered Bronze Flanged

RS Stock No: 528-901



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO plain bearing is designed for applications requiring reliable and efficient performance. Made from high-quality sintered bronze, it offers excellent durability and reduced friction, making it ideal for various industrial applications. The flanged design ensures secure positioning and easy installation.

General Specifications

Bore Size	0.31 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.56 in
Width	3/8 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

