

Circular Saw LXT®

DSS610

18V • 3 700 min⁻¹ • 165 mm

Efficient and compact professional saw

An efficient cordless circular saw for wood. Accepts blades with 165 mm diameter that achieve a max. cutting depth of 57 mm. Ventilation air is guided through the front to keep the cut line clear and an LED light offers added illumination.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	57 mm
Max. Cutting Depth at 45°	40 mm
Max. Cutting Depth at 50°	36 mm
Max. Bevel Range (Left)	0 - 50 °
No load speed	3700 min ⁻¹
Sound Power Level (L _{WA})	102 dB(A)
Sound Pressure Level (L _{pA})	94 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,0 - 3,4 kg
Product Dimensions (L x W x H):	347 x 202 x 228 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Blade Diameter	165 mm

User benefits

- Built-in dust blower clears the line of cut for greater accuracy
- Rigid aluminium base provides smooth cutting thanks to its lightness, toughness and good bend resistance
- Compact and lightweight design
- Removable dust extraction connection
- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing